

Alfa Laval SaniMicro

Rotary Spray Head

Introduction

The Alfa Laval SaniMicro is a rotary spray head tank cleaning machine for hygienic environments. Designed to clean tanks from 0.05–1 $\rm m^3.$

The Alfa Laval SaniMicro minimizes the consumption of water and cleaning media. Easy to customize to meet customer requirements, the SaniMicro allows companies to spend less time cleaning and more time producing.

Application

The Alfa Laval SaniMicro is designed for the removal of residues from hygienic tanks across the dairy, brewery, distillery, beverage, food, personal care and many other industries.

Benefits

- 40% faster cleaning = more time for production
- Saves up 40% of your cleaning cost
- Dynamic cleaning performance and 360° full wetting
- Easy to retrofit traditional spray balls to a more economical solution

Standard design

Different choice of spray pattern suitable for various applications and tank designs, ranging from simple tanks to more complex tanks with structure such as agitator and baffles. The SaniMicro is lubricated by the cleaning media.

Working principle

The flow of the cleaning media causes the head of the Alfa Laval SaniMicro to rotate, and the fan-shaped jets layout a swirling pattern throughout the tank or reactor. This generates the wetting/impact needed for the efficient removal of the residual product; the cascading flow covers all internal surface of the vessel.

Spray Pattern



360°



270° up



180° down



Certificates

2.2 material certificate, Q-doc and ATEX.





TECHNICAL DATA

Max. 2.5 m
Max. effective 0.6 m

Pressure				
Working pressure:	1 - 3 bar			
Recommended pressure:	2 bar			

PHYSICAL DATA

Materials:	AISI 316L (UNS S31603), PTFE ¹
¹ FDA compliance 21CFR§177	
Clip parts:	316
Standard Surface finish	
Exterior:	Ra 0.5 µm
Internal:	Ra 0.8 µm
Temperature	
Max. working temperature:	95 °C
Max. ambient temperature:	140 °C
Weight:	75 g
Connections	
• Thread: 3/8" Rp (BSP), or 3/8" NPT	

• Weld-on: 3/4" ISO 2037, or DN15 DIN11850-R1 or R2, or 3/4" BPE US


• Clip-on: 3/4" ISO 2037, or DN15 DIN11850-R1 or R2, or 3/4" BPE US

Caution

Avoid hydraulic shock, hard and abrasive particles in the cleaning liquid, as this can cause increased wear and/or damage of internal mechanisms. In general, a filter in the supply line is recommended. Do not use for gas evacuation or air dispersion. For steaming we refer to the manual.

Qualification Documentation

Documentatio	n specification				
	Equipment Documentation includes:				
	• EN 1935/2004 DoC				
	EN 10204 type 3.1 inspection Certificate and DoC				
	FDA DoC				
Q-doc	• GMP EC 2023/2006 DoC				
	• EU 10/2011 DoC				
	ADI DoC				
	QC DoC				
	ATEX approved machine for use in explosive atmospheres				
ATEX	Catagory 1 for installation in zone 0/20 in accordance with Directive 2014/34/EU				
AIEA	Ⅱ 1G Ex h ⅡC 85 °C175 °C Ga				
	II 1D Ex h IIIC T85 °CT140 °C Da				



For Clip-on models, the flow rate is increased by approx. 0.2 m3/h

Dimensions (mm)




Figure 1. Thread




Figure 2. Clip-on







Figure 3. Weld-on

TH		ID		OD x t	
3/8" Rp (BSP)		ISO:	Ø17.4 mm	ISO:	Ø17.2 x 1 mm
3/8" NPT		DIN Range 1:	Ø18.2 mm	DIN Range 1:	Ø18 x 1 mm
		BPE US / DIN Range	e 2: Ø19.2 mm	DIN Range 2:	Ø19 x 1.5 mm
				BPE US:	Ø19.05 x Ø1.65 mm
Туре	Α	В	E	F	G

Туре	A	В	E	F	G
Tread	62	Ø25	11		
Clip-on	62	Ø25	11	5.9	Ø3.6
Weld-on	77.5	Ø25			

Cleaning Radius



A = 360° 270° UP 180° D

This document and its contents are subject to copyrights and other intellectual property rights owned by Alfa Laval Corporate AB. No part of this document may be copied, re-produced or transmitted in any form or by any means, or for any purpose, without Alfa Laval Corporate AB's prior express written permission. Information and services provided in this document are made as a benefit and service to the user, and no representations or warranties are made about the accuracy or suitability of this information and these services for any purpose. All rights are reserved.

200006942-1-EN-GB



ALFA ENGENHARIA

Rua Dom Pedro Henrique de Orleans e Bragança, 809 - CEP 05117-002 - Vila Jaguara - São Paulo-SP www.alfaengenharia.com.br - contato@alfaengenharia.com.br Tel:+55 11 3644-5476

© Alfa Laval Corporate AB